

MARKUSSON

Link Sharpener LS 125


Mount Link Sharpener MD 20 on bench or something similar. It must sit stable. Place must be well lightened and free from easy flammable items!

! Always use protection gloves and protection glasses, when using this machine. Link Sharpener MD 20 its fitted the most various sizes of driveline its fitted best for 404 chain.

Starting.

Start the machine and carefully place the driveline between grinding wheels A and between the washers B.

Carefully move the chain manual one lap so the easy damage on the drivelines grinds away.



Data:

Voltage: 120V-60Hz

Rpm: 3450

Power: 250W

Modell LS 125